

SPEED

TAMPON PRINTING MACHINES



TAMPON PRINTING MACHINES
ACCESSORIES
SERVICE

The fastest clocked tampon printing machine on the market

Electromechanical drive

High number of parts, highest registration accuracy

technologies for your future
made in germany

ORIGINAL

TAMPOPRINT®

Tampon printing machines
ALFALAS® Laser Systems
Automations

STANDARD

SPEED -SERIES

HER PULSE: 9000

There is only one

There was a need for coming up with a tampon printing machine, the basis of which opens up new target markets for us both technologically and in terms of applications. This has cut down flat-bed printing's negative distance in performance to rotary printing in terms of part output.

The result: the development of the "Speed 40-2" tampon printing machine. Its output: as many as 9,000 cycles/h in continuous run. The production quantity is as many as 18,000/h printed parts (single colour with a printed image size of Ø 38 mm). Very high true-to-register printing, precision contours and photo and line images.

The "Speed" is a built-in execution, suitable for any kind of clocked, linear or rotary transfer systems. Thanks to its integrable misprint device there is no stopping of the machine in the absence of a workpiece.

The power costs are low in comparison to the cycle number (part output). The "Speed 40-2" is a fast shortstroke machine of a new series of tampon printing machines.

No other tampon printing machine on the market offers these benefits.



Speed at the index table ...



Speed at the ring ...

Automation with 4-fold use
36.000 parts/h



... proven speed change system

Reference automation for
small parts with rotary
index table

... 2 in one sweep

Speed guaranteed ... misprint device



"Speed Modul 2010"
standardised automation
assembly with high-
speed NC index table



Built-in execution
"Speed 40-2" with control
system and frequency
converter

TECHNOLOGY

SPEED -SERIES

Speed 40-2		Speed 40-2	Speed 40-2	Speed 40-2	Speed 40-2
Article No. Integrated model		01 06 10	01 06 11 ¹⁾	01 06 12	01 06 13
Misprint device		optional	optional	optional	optional
Single cycle		yes	yes	yes	yes
Multiple printing		yes	yes	yes	yes
Continuous run		yes	yes	yes	yes
Piece counter		--	yes	--	--
Variable speed control		external	yes	external	--
Number of cycles/hour	max.	1.500 - 9.000	1.500 - 9.000	1.500 - 9.000	1.500 - 9.000
Ink/doctoring cup	∅ mm	2 x ∅ 42	2 x ∅ 42	2 x ∅ 42	2 x ∅ 42
Variable doctoring contact pressure		no	no	no	no
Cliché size	mm	150 x 110	150 x 110	150 x 110	150 x 110
Print image size max.	∅ mm	2 x ∅ 37	2 x ∅ 37	2 x ∅ 37	2 x ∅ 37
Tampon stroke onto workpiece	mm	60	60	60	60
Tampon stroke onto cliché	mm	23	23	23	23
Tampon installation height max.	mm	60	60	60	60
Force of pressure per tampon/machine	N	270/550	270/550	270/550	270/550
Drive (see below)		electromechanic	electromechanic	electromechanic	externally driven
Connected load	kW	0,6	1,0	1,0	--
Power supply	V/phase	400V/3/N/PE	400V/3/N/PE	400V/3/N/PE	--
Interface		--	D-SUB 37-pole	--	--
Power frequency	Hz	50-60	50-60	50-60	--
Control		--	PLC	--	--
Control voltage	V/DC	--	24	24	--
Prefuse	A	16	16	16	--
Pneumatic supply fine filter 5 µm	bar	6*	6*	6*	6*
Air consumption/cycle	NL	0,1*	0,1*	0,1*	0,1*
Width	mm	297	297	297	297
Depth	mm	430	430	430	430
Height	mm	592	592	592	592
Weight	approx. kg	38	38	38	38

* if option misprint device is used // ¹⁾ Stand-Alone

Drive Description	Drive with AC asynchronous motor and resolver, without controller; without connecting cable; without control cabinet	Drive with AC asynchronous motor and frequency converter; connecting cable (5 m) with plug connection at the machine; with control cabinet	Drive with AC asynchronous motor and servo controller; connecting cable (5 m) with plug connection at the machine; without control cabinet	Without motor, externally driven (input shaft gear)

Scope of supplies:

- 2 Ink/doctoring cup
- 1 Hold-down bridge client-specific version
- 1 Tampon bridge client-specific version
- 1 Assembly table 09 02 10
- 1 Gripping tongs 09 02 20
- 2 Tampon 08 5 397
- Tools and accessories set
- Technical documentation

Accessories & Options

- Machine stand made of aluminium profiles
- Frame made of steel, closed, with angle table
- Aluminium cross table for the positioning of jigs
- Mounting plate for jig
- Misprint device
- Overhead model



TAMPOPRINT® AG

Lingwiesenstraße 1
70825 Korntal-Münchingen, GERMANY
☎ +49 7150 928-0
Fax: +49 7150 928-400
E-Mail: info@tampoprint.de
"Ventes et Affaires Françaises"
☎ +49 7150 928-144
Fax: +49 7150 928-432
E-Mail: ventes@tampoprint.de
http: www.tampoprint.de

TAMPOPRINT® INTERNATIONAL CORP.

1400 26th Street, Vero Beach, FL 32960, USA
☎ +1 772 778-8896, 800 810-8896
Fax: +1 772 778-8289
E-Mail: sales@tampoprint.com
http: www.tampoprint.com

TAMPOPRINT® IBERIA S.A.U.

c/Caspe 127-135 local B, 08013 Barcelona, SPAIN
☎ +34 93 2327161
Fax: +34 93 2471500
E-Mail: tampoprint@tampoprint.es
http: www.tampoprint.es

Dealer:



The reproduction of trademarks and brands used in this brochure, even if not explicitly expressed, does not justify the assumption that such names or symbols may be considered as free as defined by the Trademark Act and may therefore freely be used. The rights are the property of the respective owner.

TAMPOPRINT® products are permanently updated to keep pace with the latest technological developments. For this reason, figures and descriptions are non-binding. Our machines are manufactured based on the currently valid European Machinery Directives as well as the European product standards EN 1010 - 1 and EN 1010 - 2.

Subject to alterations! ©Copyright